Biresin® CR201

Composite resin system for heat curing

Product Description

Biresin® CR201 is a three component, anhydride cured, low viscosity epoxy resin system suitable for the production of high performance fibre reinforced composites with outstanding heat resistance.

Application Areas

Biresin® CR201 system is particularly suited to the filament winding process due to its low viscosity, good fibre wetting capabilities and very long potlife.

Features / Advantages

- Biresin® CR201 has a very high glass transition temperature of up to 200°C
- The reactivity of the system can be adjusted by modifying the level of the accelerator (C) Biresin® CA144
- Fast infiltration of dry fibres due to good wetting characteristics, low mixed viscosity and an elevated processing temperature

Physical Data		Resin (A)	Hardener (B)	Accelerator (C)	
Individual Components		Biresin® CR201	Biresin® CH141	Biresin® CA144	
Mixing Ratio, parts by	Weight	100	115	0.5 - 2	
Mixing Ratio, parts by	Volume	100	112	0.6 - 2.3	
Colour		transparent	yellowish	yellowish	
Viscosity, 25°C	mPas	~200	~10	<10	
Density, 25°C	g/ml	1.17	1.20	1.03	
			Mixture		
Potlife, 100 g / RT, approx. values	h		> 24		
Mixed viscosity, 25°C, approx. values		mPa.s	~100		

Typical Mechanical Properties of Cured Neat Resin, after 1 hr / 100°C + 6 hr / 180°C					
Biresin® CR201 resin (A)	with Biresin® CH141 hard	lener (B) ar	nd Biresin® CA144 accelerator (C)		
Tensile strength	ISO 527	MPa	50		
Tensile E-Modulus	ISO 527	MPa	2,850		
Elongation at break	ISO 527	%	1.9		
Flexural strength	ISO 178	MPa	115		
Flexural E-Modulus	ISO 178	MPa	3,150		
Compressive strength	ISO 604	MPa	150		
Density	ISO 1183	g/cm³	1.2		
Shore hardness	ISO 868	-	D 88		
Impact resistance	ISO 179	kJ/m²	8		



Typical Thermal Properties of Cured Neat Resin, after 1 hr / 100°C + 6 hr / 180°C						
Biresin® CR201 resin (A)	with Biresin® CH141 hardener (B) and Biresin® CA144 accelerator (C)					
Heat distortion temperature	ISO 75A	°C	188			
	ISO 75B	°C	193			
	ISO 75C	°C	172			
Glass transition temperature	ISO 11357	°C	201			

Postcuring

The suitable cure cycle and the attainable mechanical and thermal values depend on various factors, such as laminate thickness, fibre volume, reactivity of the resin system etc.

An appropriate cure cycle could look as follows:

- Heat-up rate of ca. 0.2°C/Minute until approx. 10°C below the required glass transition temperature (Tg)
- Followed by a dwell at that temperature of between 2 and 12 hours.
- Part(s) should then be cooled at ~0.5°C per minute

The specific postcure can be adapted to the required technical and economic requirements.

To measure the mechanical performance of the resin system a Sika Advanced Resins standard cycle is used to ensure that the full Tg potential of the system in question is reached.

Processing

- The material and processing temperatures should be in the range 18 35°C.
- The mixing ratio must be followed accurately to obtain best results. Deviating from the correct mix ratio will lead to lower performance.
- Before demoulding precuring of at least 2 h at 90°C is recommended.
- The final mechanical and thermal values are dependent on the applied postcuring cycles.
- It is recommended to clean brushes or tools immediately after use with Sika Reinigungsmittel 5.
- Additional information is available in "Processing Instructions for Composite Resins".

Packaging (net weight, kg)				
Biresin® CR201 resin (A)	1,000	200		10
Biresin® CH141 hardener (B)	1,100	220		9
Biresin® CA144 accelerator (C)			10	0.2

Storage

- Minimum shelf life of Biresin® CR201 resin (A) is 24 month and of Biresin® CH141 hardener (B) and CA144 accelerator (C) is 12 month under room conditions (18 25°C), when stored in original unopened containers.
- After prolonged storage at low temperature, crystallisation of resin (A) may occur. This is easily removed by warming up for a sufficient time at a minimum of 60-80°C.
- Containers must be closed tightly immediately after use. The residual material needs to be used up as soon as possible.

Health and Safety Information

For information and advice on the safe handling, storage and disposal of chemical products, users shall refer to the most recent Safety Data Sheet (SDS) containing physical, ecological, toxicological and other safetyrelated data.



Disposal considerations

Product Recommendations: Must be disposed of in a special waste disposal unit in accordance with the corresponding regulations.

Packaging Recommendations: Completely emptied packagings can be given for recycling. Packaging that cannot be cleaned should be disposed of as product waste.

Value Bases

All technical data stated in this Product Data Sheet are based on laboratory tests. Actual measured data may vary due to circumstances beyond our control.

Legal Notice

The information, and, in particular, the recommendations relating to the application and end-use of Sika products, are given in good faith based on Sika's current knowledge and experience of the products when properly stored, handled and applied under normal conditions in accordance with Sika's recommendations. In practice, the differences in materials, substrates and actual site conditions are such that no warranty in respect of merchantability or of fitness for a particular purpose, nor any liability arising out of any legal relationship whatsoever, can be inferred either from this information, or from any written recommendations, or from any other advice offered. The user of the product must test the product's suitability for the intended application and purpose. Sika reserves the right to change the properties of its products. The proprietary rights of third parties must be observed. All orders are accepted subject to our current terms of sale and delivery. Users must always refer to the most recent issue of the local Product Data Sheet for the product concerned, copies of which will be supplied on request.

Further information available at:

Sika Deutschland GmbH

 Subsidiary Bad Urach
 Tel:
 +49 (0) 7125 940 492

 Stuttgarter Str. 139
 Fax:
 +49 (0) 7125 940 401

 D - 72574 Bad Urach
 Email:
 tooling@de.sika.com

 Germany
 Internet:
 www.sika.com



